# **Technical Data**



### Performance you can trust

## **EASYLINE®** Disabled Stencil

Part Code: 40147

 No of Pages
 01

 Issue No
 03

 Date
 5/13

 Ref
 ELDS

### Description

The EASYLINE® Disabled Stencil is made from strong, re-usable polypropylene, making marking quick and simple.

### Features and Benefits

- Made from durable polypropylene
- · Stencil can be re-used once the paint has dried

### Technical Data (Typical)

Stencil Image Size:	1000 (H) x 850 (W) mm
Material:	Polypropylene

### Surface Preparation

All surfaces should be clean, dry and dust free before application.

Any surfaces covered in heavy grime/grease should be cleaned with a suitable cleaner solution.

For best results use with the EASYLINE® range of aerosol paints and hand held applicator.

### **Application Guidelines**

- Place stencil into the required position.
- Weigh stencil down to ensuring that it lays flat.
- Shake can until metal balls rattle, then shake for one further minute.
- Holding the can in an inverted position apply spray within the cut-out area using a uniform spray pattern until completely covered.
- After use, clear nozzle by holding can upright and depressing the button for 3 seconds.
- After 20 minutes carefully remove stencil, lifting vertically to prevent any dragging of the paint.
- Leave stencil to dry before re-packing.

The EASYLINE® Disabled Stencil can be re-used once the paint has dried.

### Advice

If further advice or information is required, please contact our Customer Service Department.

**Disclaimer:** The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which may affect the use and performance of our products, for this reason it is given without responsibility.

T +44 (0) 113 232 2600 F +44 (0) 113 232 2740 E customer-service@rocol.com www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

BS EN ISO 9001 Certificate No. FM 12









ROCOL A division of TW Ltd